### audison.com







## TH K2 II P Coro

300 W Max Power



TECHNICAL SPECIFICATIONS					
Component	2-way system				
Size					
Woofer	mm (in.)	165 (6.5)			
Tweeter diaphragm	mm (in.)	18 (1.5)			
Crossover	mm (in.)	348x190x66,5 (13.7x7.48x26.18)			
Voice Coil Ø					
Woofer	mm (in.) 50 (2)				
Tweeter	mm (in.) 34 (1.34)				
Power Handling	W peak	300			
	W continuos	150			
Sensitivity	dB SPL	87			
Impedance	Ω	4			
Frequency Response	Hz	40 ÷ 26k			
Crossover	Woofer Cut-off Cut-off	Lo-pass 1,35kHz @ 6 dB/Oct. Hi-pass 2.8 kHz @ 12 dB/Oct. Q=2.06			
Crossover - Adjustment	Contour @1 Khz	-3/-1,5/0 dB			
	Tweeter level	-4/-2/0/+1,5 dB			
Weight of one component					
Woofer	kg (lb)	1.25 (2.76)			
Tweeter	kg (lb)	0,335 (0.78)			
Crossover	kg (lb)	3,6 (7)			

ELECTRO-ACOUSTIC PARAMETERS		TH 6.5 II Sax	TH 1.5 II Violino	
			Bottom Case	Bottom Disk
D	mm	130	38	38
Xmax	mm	5,4	-	-
Re	Ω	3,8	6,1	6,1
Fs	Hz	55	780	980
Le	mH	0,43	0,025	0,025
Vas	1	8,6	0,019	0,013
Mms	g	24,2	0,43	0,43
Cms	mm/N	0,35	0,09	0,062
BL	T•m	8,2	3,32	3,44
Qts		0,43	0,83	0,97
Qes		0,47	1,2	1,3
Qms		5,3	2,9	3,5
Spl	dB	87	92,5	93

#### TH 1.5 II violino

- 34 mm CCAW single layer voice coil combining light weight, stability 1. at lower frequencies and total absence of musical transients compression.
- Extremely powerful custom N38 "H-grade" Neodymium magnet providing 1.67 T+m in the magnetic gap for superb dynamic response and very low distortion in the whole frequency range. Exclusive air-loading system resulting in a resonance frequency below 800 Hz, for filter set-up starting as low as 1.5 kHz 12dB/Oct. 38 mm natural silk dome optimized with extensive material becreateriation. Incerv ubcreater company and Einite Element Analyzie 2.
- 3.
- 4. characterization, laser vibrometer scanning and Finite Element Analysis methods for a smooth and extended response.
- Frequency response up to 26 kHz optimized for off-axis installation. TH 1.5 II Violino Tuning System featuring two types of electro-5 6. acoustic load: bottom case or bottom disk according to targets of highest performance as well as flexibility of in-car integration.
- 7. Full solid metal construction structure with each part exclusively designed and produced for the Audison TH 1.5 II.
- 8. FEM (Finite Element Method) optimized faceplate and front spokes for an improved dispersion pattern.
- eID technology providing TH 1.5 II traceability starting from the manufacturing stage up to the owner. 9.

#### TH 6.5 II sax

- 50 mm mobile voice coil in CCAR (Copper Clad Aluminum Ribbon) wound with flat wire to maximize the force factor and heat dissipation. 1. 2.
- Low inductance of the mobile voice coil to optimize the emission in medium-high band (2-3 kHz). 3. N48 "H-grade" neodymium magnet with superb thermal stability to
- guarantee an optimal dynamic reserve in every situation. Magnetic group geometry designed using finite element simulation software to maximize efficiency by concentrating the magnetic field in 4.
- the gap Membrane made of TPX®, a transparent material that reduces the 5. frequency response irregularities in the mid-high band, leaving the speaker interior in full view.
- 6.
- Membrane geometry designed using simulation software, to obtain a smooth emission over all the listening angles. Basket made of a single piece of die-cast aluminium featuring four pairs of spokes to optimize heat transfer, nullify turbulent airflows and 7.
- ensure maximum structural rigidity. Hi-excursion suspension and spider, optimized with simulations of the 8.
- loudspeaker multi-physical behavior. eID technology providing TH 6.5 II traceability starting from the 9. manufacturing stage up to the owner.

#### **THX 2 II**

- Construction without compromise with the use of high quality resistors, 1. capacitors and inductors.
- Use of compensation networks for both woofer and tweeter, which 2. optimize the load seen by the amplifier.
- Best Envelopment filtering configuration with a well-distributed vertical scene along the entire height of the passenger compartment. 3. 4 emission levels for the tweeter ( -4, -2 , 0, +1,5 dB), designed using 4.
- L-Pad technique. mid-frequency level control (-3 -> 0 dB) centered at 900 Hz. 5.
- Possibility of bi-amplification. 6.



#### Elettromedia 62018 Potenza Picena (MC) Italy

T +39 0733 870 870 - F +39 0733 870 880 elettromedia.com

# audison